


MSC C6B-KLH

Intel® Core™ 7th Generation



✂ 125 x 95

⚡ 35 / 55 W

🔌 0 +60



IoT Solutions
Alliance

COM Express

Description

The MSC C6B-KLH module is based on Intel's 7th generation Core processor family. The Intel two-chip solution allows highest performance in graphics and computing on a COM Express module in basic form factor.

The new MSC C6B-KLH offers triple independent display support with up to 4k x 2k resolution, highest level graphics acceleration and hardware based video en-/decoding. Fast DDR4 memory with optional error correction (ECC) and multiple USB 3.0/2.0 interfaces complete the compact and powerful module.

Different dual- and quad-core processors are supported by this design. Besides an extensive set of interfaces and features, the MSC C6B-KLH optionally offers hardware based security compliant to the requirements of TCG (Trusted Computing Group).

The Type 6 pin-out allows direct access to the latest digital display interfaces like DisplayPort 1.3, HDMI 1.4b and DVI as well as up to four USB 3.0 interfaces supporting the fastest peripherals currently available.

Highlights

- Intel® Core™ i7-7820EQ (quad-core, 3.0/3.7GHz, 45/35W cTDP),
- Intel® Core™ i5-7440EQ (quad-core, 2.9/3.6GHz, 45/35W cTDP),
- Intel® Core™ i5-7442EQ (quad-core, 2.1/2.9GHz, 25W TDP),
- Intel® Core™ i3-7100E (dual-core, 2.9GHz, 35W TDP),
- Intel® Core™ i3-7102E (dual-core, 2.1GHz, 25W TDP),
- Intel® Xeon® E3-1505Mv6 (quad-core, 3.0/4.0GHz, 45/35W cTDP),
- Intel® Xeon® E3-1505Lv6 (quad-core, 2.2/3.0GHz, 25W TDP)
- Intel® HD Graphics 630, P630
- Intel® chipsets QM175, HM175 or CM238
- Up to 32GB DDR4-2400 SDRAM, dual channel (ECC optional)
- Four SATA 6Gb/s mass storage interfaces
- Three DisplayPort/HDMI/DVI interfaces
- Embedded DisplayPort / LVDS (24 Bit, dual channel) interface
- Triple independent display support
- DirectX 12, OpenGL 4.4, OpenCL 2.x
- Resolution up to 4096 x 2304
- Eight PCI Express™ x1 lanes; PEG x16
- Four USB 3.0/2.0 and four USB 2.0 interfaces
- Trusted Platform Module
- UEFI Firmware

Technical Data - MSC C6B-KLH

Technology	x86
Formfactor	COM Express Basic
CPU	<p>Intel® Core™ i7-7820EQ (quad-core, 3.0/3.7GHz, 8MB cache, 45/35W cTDP), Intel® Core™ i5-7440EQ (quad-core, 2.9/3.6GHz, 6MB cache, 45/35W cTDP), Intel® Core™ i5-7442EQ (quad-core, 2.1/2.9GHz, 6MB cache, 25W TDP), Intel® Core™ i3-7100E (dual-core, 2.9GHz, 3MB cache, 35W TDP), Intel® Core™ i3-7102E (dual-core, 2.1GHz, 3MB cache, 25W TDP), Intel® Xeon® E3-1505Mv6 (quad-core, 3.0/4.0GHz, 8MB cache, 45/35W cTDP), Intel® Xeon® E3-1505Lv6 (quad-core, 2.2/3.0GHz, 8MB cache, 25W TDP)</p> <p>Intel® Technologies: Intel® vPro*, Intel® 64, Intel® Virtualization Technology (VT-x)*, Intel® Virtualization Technology for Directed I/O (VT-d)*, Intel® Trusted Execution Technology*, Intel® Adv. Encryption Standard AES-NI*, Intel® Turbo Boost Technology 2.0*</p> <p>* not on all models</p>
Chipset	Intel® Platform Controller Hubs (PCH) QM175, HM175 or CM238
RAM	2x 260-pin SO-DIMM socket for up to 2x 16GB DDR4 SDRAM (DDR4-2400); dual channel operation; ECC option
Storage Interfaces	4x SATA channels (up to 6Gb/s)
USB	4x USB 3.0/2.0, 4x USB 2.0
Serial Interfaces	2x high-speed serial ports from PCH
Bus Interfaces	8x PCI Express x1 Gen 3, 1x PCI Express Graphics (PEG) x 16 Gen. 3 LPC bus (Low Pin Count bus; no DMA support)
Display Controller	<p>Integrated Intel HD graphics Gen. 9 3D Acceleration: DirectX® 11/12, OpenGL 4.3/4.4, OpenGL ES 2.0, OpenCL 2.x; Video Decode: H.264 @ Level 5.2, H.265/HEVC 10-bit, MPEG2, VC1/WMV, JPEG, VP8, VP9 10-bit; Video Encode: H.263, H.264, VP8, AVC JPEG, VP9 GPU-accelerated.</p> <p>Triple independent display support</p>
Display Interfaces	<p>Display Port and HDMI/DVI: 3x Digital Display Interface, usable as DisplayPort 1.2 (up to 4096 x 2304 @ 60Hz), also usable as HDMI 1.4b or DVI (up to 4096 x 2160 @ 30Hz) 1x Embedded DisplayPort 1.4 (on variants without LVDS only); 4096 x 2304 @ 60Hz</p> <p>LCD: LVDS 24bit, dual-channel (not on all variants); 1920 x 1200 @ 60Hz</p>
Network Interface	10/100/1000Base-TX (integrated in PCH, Intel® i219LM PHY)
Audio Interface	High Definition Audio
Security Device	TPM 1.2

Miscellaneous	<p>Watchdog Timer: Initiates system reset, programmable</p> <p>Fan Supply: 4-pin header for 12V CPU fan, PWM speed controlled and PWM speed control for system fan supported</p> <p>RTC battery: External</p> <p>System Monitoring: Voltage, temperature, CPU fan, system fan</p>
Firmware	<p>UEFI Firmware: AMI Aptio[®] V</p> <p>Security: TPM 1.2 support, TCG compliant</p> <p>Power Management: ACPI Active fan control</p> <p>USB: USB legacy support (keyboard, mouse, storage)</p> <p>Monitoring: System Monitoring Health Monitoring</p> <p>MSC Adv. Boot Device Selection: Boot device priority setting based on physical interfaces</p>
OS Support	<p>Windows 10 (embedded) BSP for Linux (Yocto) EAPI (HW Programming Interface)</p>
Power Requirement	<p>Voltage: +12V +/-10%, 5V Stby optional,</p> <p>Power Consumption: 35 W to 55 W (typ.)</p>
Environment	<p>Ambient Temperature: 0° ... 60°C (operating), -25° ... 85°C (storage)</p> <p>Humidity: 5 ... 95% (operating, non-condensing), 5 ... 95% (storage, non-condensing)</p>
Dimensions	125mm x 95mm x 13mm
Certificates	UL / CE

Order Reference - MSC C6B-KLH

Order Number	Description	Reference	Cat
70288	COM Express Type 6 Basic module (125mm x 95mm); CPU: Intel Core i3-7102E, dual-core, 2.1GHz, 25W TDP; Chipset: HM175; Graphics: integrated Intel HD Gen 9 (GT2); LVDS; 3x DP/HDMI/DVI; Ethernet: Intel i219 Gbit; HD audio; 4x SATA; 4x USB3/2, 4x USB2; 8x PCIe x1 Gen 3; PEG x16 Gen 3; 2x socket for DDR4 SO-DIMM.	MSC C6B-KLH-7102E-NN0201C PCBFTX	OR
70304	COM Express Type 6 Basic module (125mm x 95mm); CPU: Intel Core i3-7100E, dual-core, 2.9GHz, 35W TDP; Chipset: HM175; Graphics: integrated Intel HD Gen 9 (GT2); LVDS; 3x DP/HDMI/DVI; Ethernet: Intel i219 Gbit; HD audio; 4x SATA; 4x USB3/2, 4x USB2; 8x PCIe x1 Gen 3; PEG x16 Gen 3; 2x socket for DDR4 SO-DIMM.	MSC C6B-KLH-7100E-NN0201C PCBFTX	OR
70296	COM Express Type 6 Basic module (125mm x 95mm); CPU: Intel Core i5-7442EQ, quad-core, 2.1/2.9GHz, 25W TDP; Chipset: QM175; Graphics: integrated Intel HD Gen 9 (GT2); LVDS; 3x DP/HDMI/DVI; Ethernet: Intel i219 Gbit; HD audio; 4x SATA; 4x USB3/2, 4x USB2; 8x PCIe x1 Gen 3; PEG x16 Gen 3; 2x socket for DDR4 SO-DIMM.	MSC C6B-KLH-7442EQ-NN0201C PCBFTX	OR
70298	COM Express Type 6 Basic module (125mm x 95mm); CPU: Intel Core i5-7440EQ, quad-core, 2.9/3.6GHz, 45W TDP; Chipset: QM175; Graphics: integrated Intel HD Gen 9 (GT2); LVDS; 3x DP/HDMI/DVI; Ethernet: Intel i219 Gbit; HD audio; 4x SATA; 4x USB3/2, 4x USB2; 8x PCIe x1 Gen 3; PEG x16 Gen 3; 2x socket for DDR4 SO-DIMM.	MSC C6B-KLH-7440EQ-NN0201C PCBFTX	OR
70292	COM Express Type 6 Basic module (125mm x 95mm); CPU: Intel Core i7-7820EQ, quad-core, 3.0/3.7GHz, 45W TDP; Chipset: QM175; Graphics: integrated Intel HD Gen 9 (GT2); LVDS; 3x DP/HDMI/DVI; Ethernet: Intel i219 Gbit; HD audio; 4x SATA; 4x USB3/2, 4x USB2; 8x PCIe x1 Gen 3; PEG x16 Gen 3; 2x socket for DDR4 SO-DIMM.	MSC C6B-KLH-7820EQ-NN0201C PCBFTX	OR
70284	COM Express Type 6 Basic module (125mm x 95mm); CPU: Intel Xeon E3-1505Lv6, quad-core, 2.2/3.0GHz, 25W TDP; Chipset: CM238; Graphics: integrated Intel HD Gen 9 (GT2); LVDS; 3x DP/HDMI/DVI; Ethernet: Intel i219 Gbit; HD audio; 4x SATA; 4x USB3/2, 4x USB2; 8x PCIe x1 Gen 3; PEG x16 Gen 3; 2x socket for DDR4 or DDR4ECC SO-DIMM.	MSC C6B-KLH-1505LV6-NN1201C PCBFTX	OR

Order Reference - MSC C6B-KLH

Order Number	Description	Reference	Cat
70306	COM Express Type 6 Basic module (125mm x 95mm); CPU: Intel Xeon E3-1505Mv6, quad-core, 3.0/4.0GHz, 45W TDP, 35W cTDP; Chipset: CM238; Graphics: integrated Intel HD Gen 9 (GT2); LVDS; 3x DP/HDMI/DVI; Ethernet: Intel i219 Gbit; HD audio; 4x SATA; 4x USB3/2, 4x USB2; 8x PCIe x1 Gen 3; PEG x16 Gen 3; 2x socket for DDR4 or DDR4ECC SO-DIMM.	MSC C6B-KLH-1505MV6-NN1201C PCBFTX	OR
70302	COM Express Type 6 Basic module (125mm x 95mm); CPU: Intel Core i3-7102E, dual-core, 2.1GHz, 25W TDP; Chipset: HM175; Graphics: integrated Intel HD Gen 9 (GT1); eDP; 3x DP/HDMI/DVI; Ethernet: Intel i219 Gbit; HD audio; 4x SATA; 4x USB3/2, 4x USB2; 8x PCIe x1 Gen 3; PEG x16 Gen 3; 2x socket for DDR4 SO-DIMM.	MSC C6B-KLH-7102E-NN0101C PCBFTX	OR
70286	COM Express Type 6 Basic module (125mm x 95mm); CPU: Intel Core i3-7100E, dual-core, 2.9GHz, 35W TDP; Chipset: HM175; Graphics: integrated Intel HD Gen 9 (GT2); eDP; 3x DP/HDMI/DVI; Ethernet: Intel i219 Gbit; HD audio; 4x SATA; 4x USB3/2, 4x USB2; 8x PCIe x1 Gen 3; PEG x16 Gen 3; 2x socket for DDR4 SO-DIMM.	MSC C6B-KLH-7100E-NN0101C PCBFTX	OR
70290	COM Express Type 6 Basic module (125mm x 95mm); CPU: Intel Core i5-7442EQ, quad-core, 2.1/2.9GHz, 25W TDP; Chipset: QM175; Graphics: integrated Intel HD Gen 9 (GT2); eDP; 3x DP/HDMI/DVI; Ethernet: Intel i219 Gbit; HD audio; 4x SATA; 4x USB3/2, 4x USB2; 8x PCIe x1 Gen 3; PEG x16 Gen 3; 2x socket for DDR4 SO-DIMM.	MSC C6B-KLH-7442EQ-NN0101C PCBFTX	OR
70300	COM Express Type 6 Basic module (125mm x 95mm); CPU: Intel Core i5-7440EQ, quad-core, 2.9/3.6GHz, 45W TDP; Chipset: QM175; Graphics: integrated Intel HD Gen 9 (GT2); eDP; 3x DP/HDMI/DVI; Ethernet: Intel i219 Gbit; HD audio; 4x SATA; 4x USB3/2, 4x USB2; 8x PCIe x1 Gen 3; PEG x16 Gen 3; 2x socket for DDR4 SO-DIMM.	MSC C6B-KLH-7440EQ-NN0101C PCBFTX	OR
70294	COM Express Type 6 Basic module (125mm x 95mm); CPU: Intel Core i7-7820EQ, quad-core, 3.0/3.7GHz, 45W TDP; Chipset: QM175; Graphics: integrated Intel HD Gen 9 (GT2); eDP; 3x DP/HDMI/DVI; Ethernet: Intel i219 Gbit; HD audio; 4x SATA; 4x USB3/2, 4x USB2; 8x PCIe x1 Gen 3; PEG x16 Gen 3; 2x socket for DDR4 SO-DIMM.	MSC C6B-KLH-7820EQ-NN0101C PCBFTX	OR

Order Reference - MSC C6B-KLH

Order Number	Description	Reference	Cat
70282	COM Express Type 6 Basic module (125mm x 95mm); CPU: Intel Xeon E3-1505Lv6, quad-core, 2.2/3.0GHz, 25W TDP; Chipset: CM238; Graphics: integrated Intel HD Gen 9 (GT2); eDP; 3x DP/HDMI/DVI; Ethernet: Intel i219 Gbit; HD audio; 4x SATA; 4x USB3/2, 4x USB2; 8x PCIe x1 Gen 3; PEG x16 Gen 3; 2x socket for DDR4 or DDR4ECC SO-DIMM.	MSC C6B-KLH-1505LV6-NN1101C PCBFTX	OR
70308	COM Express Type 6 Basic module (125mm x 95mm); CPU: Intel Xeon E3-1505Mv6, quad-core, 3.0/4.0GHz, 45W TDP, 35W cTDP; Chipset: CM238; Graphics: integrated Intel HD Gen 9 (GT2); eDP; 3x DP/HDMI/DVI; Ethernet: Intel i219 Gbit; HD audio; 4x SATA; 4x USB3/2, 4x USB2; 8x PCIe x1 Gen 3; PEG x16 Gen 3; 2x socket for DDR4 or DDR4ECC SO-DIMM.	MSC C6B-KLH-1505MV6-NN1101C PCBFTX	OR

Accessories

Order Number	Description	Reference
Carrier Options		
67295	COM Express Type 6 Evaluation Carrier Board with PCI Express x4/x16 slot, USB 3.0/2.0, GbE, SATA, DisplayPort, eDP/LVDS, VGA and HD audio interfaces; Mini PCI Express socket, SD card slot, ATX power connector and single 12V power jack. Dimensions: 170mm x 170mm (Mini-ITX form factor)	MSC C6-MB-EV-001 PCBFTX
41857	COM Express Type 6 Evaluation board with various PCI Express interfaces, SATA and mSATA, USB 2.0/3.0, Display Port and eDP, HDMI/DVI, HD-Audio, POST code display. ATX form factor	MSC C6-MB-EVA
Cooling Options		
1131080	Active Heatsink for C6B-SLH, C6B-KLH, C6B-CFLH and C6B-CFLR, consisting of a single-piece aluminum profile with fins, pressed in standoffs without thread (2.7mm inner diameter), screws and thermopads for the thermal contact to CPU and chipset. PWM fan 80x80x15mm.	MSC C6B-SLH-01 HSF-001
1131081	Passive Heatsink for C6B-SLH, C6B-KLH, C6B-CFLH and C6B-CFLR, consisting of a single-piece aluminum profile with fins, pressed in standoffs without thread (2.7mm inner diameter), screws and thermopads for the thermal contact to CPU and chipset.	MSC C6B-SLH-01 HSI-001
1131082	Heatspreader for C6B-SLH, C6B-KLH, C6B-CFLH and C6B-CFLR. Single-piece aluminum profile, pressed in standoffs without thread (2.7mm inner diameter), screws and thermopads for the thermal contact to CPU and chipset. No fan, no SO-DIMM cutout.	MSC C6B-SLH-01 HSP-001
1131083	Heatspreader for C6B-SLH, C6B-KLH, C6B-CFLH and C6B-CFLR. Single-piece aluminum profile, pressed in standoffs with M2.5 thread, screws and thermopads for the thermal contact to CPU and chipset. No fan, no SO-DIMM cutout.	MSC C6B-SLH-02 HSP-001
Memory Options		
83003	4GB DDR4-2400 SoDimm, 1.2V, ECC	M4DI-4GSSPCSJ-F
83001	8GB DDR4-2400 SoDimm, 1.2V, ECC	M4DI-8GS1PCSJ-C
83002	4GB DDR4-2400 SoDimm, 1.2V	M4SI-4GSSNCSJ-F
81883	8GB DDR4-2400 SoDimm, 1.2V	M4SI-8GSSOCSJ-F
1138365	16GB DDR4-2400 SoDimm, 1.2V	M4SS-AGS1OC0J-B
Starter Kits		
68752	Starterkit for COM Express Type 6 modules MSC C6B-SLH with Intel 6th generation Core processors. Consists of Mini-ITX platform board, suitable Heatsink with fan and two DDR4 memory modules. Please order separately the COM Express C6B-SLH module of your choice.	MSC C6-SK-SLH-EV-KIT001 SETPAC

Avnet Integrated
 MSC Technologies GmbH
 Industriestr. 16
 76297 Stutensee

integrated@avnet.eu
avnet.com/integrated